



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP74RB

7 outlet black strip, 540 joules Protect It! Surge Suppressor



Highlights

- 7 outlets (6 right-angle outlets and 1 designated transformer outlet)
- 4-ft. cord
- 540 joule rating
- \$25,000 Ultimate Lifetime Insurance (USA & Canada only)

Description

Tripp Lite's TLP74RB offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP74RB offers 7 total outlets (6 at right angle and 1 designated transformer plug outlet), 4 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 540 joules shields equipment from surges and line noise. Attractive black housing with keyhole mounting tabs offering convenient protection of desktop computer equipment and accessories. \$25,000 Ultimate Lifetime Insurance (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/4-ft. AC line cord

ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: AC: 150V RMS Clamping/540 joules/400V UL1449 Let-through

Applications

- Ideal for any desktop, network or home computing application requiring AC line protection.

Package Includes

- TLP74RB Surge Suppressor

Features

- 540 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 total AC outlets (6 right angle and 1 transformer plug outlet)
- 4 foot AC line cable
- Attractive black housing
- Lighted on/off switch with integrated circuit breaker for overload protection of all outlets
- Diagnostic LED confirms surge suppression status
- Integrated keyhole slots provide convenient wall/desk mounting
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications

- \$25,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 1 large transformer plug accessory without covering remaining outlets
Outlet orientation	Single row
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	4
Input cord length (m)	1.2
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	36000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	540
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	400V
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	

Shipping weight (lbs)	1.10
Shipping weight (kg)	0.50
Unit Dimensions (HWD/in)	1.33 x 2.04 x 12.4
Unit Dimensions (HWD/cm)	3.38 x 5.18 x 31.50
Shipping Dimensions (HWD/in)	14.05 x 3.26 x 1.37
Shipping Dimensions (HWD/cm)	35.69 x 8.28 x 3.48
Unit weight (lbs)	1.04
Unit weight (kg)	0.47
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Black
Receptacle Color	Black
AC line cord color	Black
Style	Strip
Outlets center to center measurement	28.5mm
Keyhole slot center to center measurement	207mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4522.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.