



**Tripp Lite**  
 1111 West 35th Street  
 Chicago, IL 60609 USA  
 Telephone: +(773) 869 1234  
 E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TRAVELCUBE

**1 AC outlet, direct plug-in surge suppressor with built-in tel/modem surge protection**



### Highlights

- 1 AC outlet
- Direct plug-in design
- Built-in tel/modem surge protection
- 540 joule rating
- Diagnostic LED displays protection status
- \$10,000 [Ultimate Lifetime Insurance](#) (US & Canada only)

### Description

The TRAVELCUBE is designed for convenient portable and economical surge protection. Small and powerful, the TRAVELCUBE features 540 joules and carries \$10K of insurance as well as a . Throw it in a briefcase or purse and have quality surge protection wherever you need it — hotel room, dorm, client office — anywhere!

#### Applications

- Ideal for use with laptops, fax machines, electronic notepads, personal organizers and other portable electronic devices

#### Package Includes

- TRAVELCUBE surge suppressor
- Bonus 6-ft. telephone cord

### Features

- Portable wall-mount cube stores easily in any bag or briefcase
- 1 NEMA5-15R AC outlet
- 540 joules of protection shields equipment from harmful surges, spikes and line noise
- Diagnostic LED displays protection status
- Built-in tel/modem surge protection
- Bonus 6-ft. phone cord included
- UL 1449 rated 3rd Edition
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only)

### Specifications

OVERVIEW	
Intended Application	Home/Office, Travel
OUTPUT	
Frequency compatibility	50 / 60 Hz

Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	1 NEMA 5-15R
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P input plug
Input cord length details	Direct plug-in
Voltage compatibility (VAC)	120
Maximum Surge Amps	36000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	540
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	500V
EMI / RFI filtering	Up to 20dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	.42
Shipping weight (kg)	0.19
Unit Dimensions (HWD/in)	1.49 x 2.16 x 3.07
Unit Dimensions (HWD/cm)	3.78 x 5.49 x 7.80
Shipping Dimensions (HWD/in)	2.83 x 5.12 x 6.50
Shipping Dimensions (HWD/cm)	7.19 x 13.00 x 16.51
Unit weight (lbs)	.17
Unit weight (kg)	0.08
Material of construction	Plastic

<b>Style</b>	Direct Plug-in
<b>Form factors supported</b>	Direct plug in suppressor supports wall-mounting directly into AC receptacle
<b>SPECIAL FEATURES</b>	
<b>Appearance</b>	Ultra-compact portable direct plug in protector in an attractive, grey lightweight enclosure
<b>CERTIFICATIONS</b>	
<b>UL1449 3rd Edition (AC Suppression)</b>	UL1449 3RD EDITION
<b>Approvals</b>	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$10,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2559](http://www.tripplite.com/en/products/model.cfm?txtModelID=2559).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.