

SNK Series, Terminal Blocks

Type	Cross section*	Spacing	Current*	Block		Order code	Pack ⁹⁾	End section		Pack ⁹⁾	Jumper bar IP20		
				Color	Function			Color	Order code		Nb of poles	Order code	Pack ⁹⁾
* IEC * UL/CSA (in <i>Italic</i>)													
Feed-through and ground terminal blocks													
 ZS4...	4 mm² 12 AWG	5.2 mm 0.205 in	32 A 20 A	Grey Blue Green/Yellow	Feed-through Feed-through Ground	1SNK 505 010 R0000 1SNK 505 020 R0000 1SNK 505 150 R0000	50 50 20	Dark grey	1SNK 505 910 R0000	20	2 poles 3 poles 4 poles 5 poles 10 poles 50 poles	1SNK 905 302 R0000 1SNK 905 303 R0000 1SNK 905 304 R0000 1SNK 905 305 R0000 1SNK 905 310 R0000 1SNK 905 350 R0000	50 50 50 50 30 10
 ZS6...	6 mm² 10 AWG	6 mm 0.236 in	41 A 30 A	Grey Blue Green/Yellow	Feed-through Feed-through Ground	1SNK 506 010 R0000 1SNK 506 020 R0000 1SNK 506 150 R0000	50 50 20	Dark grey	1SNK 505 910 R0000	20	2 poles 3 poles 4 poles 5 poles 10 poles 50 poles	1SNK 906 302 R0000 1SNK 906 303 R0000 1SNK 906 304 R0000 1SNK 906 305 R0000 1SNK 906 310 R0000 1SNK 906 350 R0000	50 50 50 50 20 10
 ZS10...	10 mm² 6 AWG	8 mm 0.315 in	57 A 42 A	Grey Blue Green/Yellow	Feed-through Feed-through Ground	1SNK 508 010 R0000 1SNK 508 020 R0000 1SNK 508 150 R0000	50 50 20	Dark grey	1SNK 505 910 R0000	20	2 poles 3 poles 4 poles 5 poles 10 poles	1SNK 908 302 R0000 1SNK 908 303 R0000 1SNK 908 304 R0000 1SNK 908 305 R0000 1SNK 908 310 R0000	50 50 50 40 20
 ZS16...	16 mm² 4 AWG	10 mm 0.394 in	76 A 67 A	Grey Blue Green/Yellow	Feed-through Feed-through Ground	1SNK 510 010 R0000 1SNK 510 020 R0000 1SNK 510 150 R0000	50 50 20	Dark grey	1SNK 505 910 R0000	20	2 poles 3 poles 4 poles 5 poles 10 poles	1SNK 910 302 R0000 1SNK 910 303 R0000 1SNK 910 304 R0000 1SNK 910 305 R0000 1SNK 910 310 R0000	50 50 40 30 20
 ZS35...	35 mm² 0 AWG	16 mm 0.630 in	125 A 150 A	Grey Blue Green/Yellow	Feed-through Feed-through Ground	1SNK 516 010 R0000 1SNK 516 020 R0000 1SNK 516 150 R0000	20 20 20	Closed block			2 poles 3 poles 4 poles 5 poles 10 poles	1SNK 916 302 R0000 1SNK 916 303 R0000 1SNK 916 304 R0000 1SNK 916 305 R0000 1SNK 916 310 R0000	10 10 10 10 10
 ZS70...	70 mm² 00 AWG	22 mm 0.866 in	192 A 175 A	Grey Blue Green/Yellow	Feed-through Feed-through Ground	1SNK 522 010 R0000 1SNK 522 020 R0000 1SNK 522 150 R0000	10 10 10	Closed block			2 poles 3 poles 5 poles 10 poles	1SNK 922 302 R0000 1SNK 922 303 R0000 1SNK 922 305 R0000 1SNK 922 310 R0000	5 5 5 5
 ZS95...	95 mm² 000 AWG	26 mm 1.023 in	232 A 230 A	Grey Blue Green/Yellow	Feed-through Feed-through Ground	1SNK 526 010 R0000 1SNK 526 020 R0000 1SNK 526 150 R0000	10 10 10	Closed block			2 poles 3 poles 5 poles 10 poles	1SNK 926 302 R0000 1SNK 926 303 R0000 1SNK 926 305 R0000 1SNK 926 310 R0000	5 5 5 5

Double deck terminal blocks													
 ZS4-D2...	4 mm ² 12 AWG	5.2 mm 0.205 in	29 A 20 A	Grey	Feed-through	1SNK 505 210 R0000	50	Dark grey	1SNK 505 960 R0000	20	2 poles	1SNK 905 302 R0000	50
											3 poles	1SNK 905 303 R0000	50
											4 poles	1SNK 905 304 R0000	50
											5 poles	1SNK 905 305 R0000	50
											10 poles	1SNK 905 310 R0000	30
 ZS6-D2...	6 mm ² 10 AWG	6 mm 0.236 in	41 A 30 A	Grey	Feed-through	1SNK 506 210 R0000	50	Dark grey	1SNK 505 960 R0000	20	2 poles	1SNK 906 302 R0000	50
											3 poles	1SNK 906 303 R0000	50
											4 poles	1SNK 906 304 R0000	50
											5 poles	1SNK 906 305 R0000	50
											10 poles	1SNK 906 310 R0000	20