

**Disconnect
switches
Fusible**

Standard handles & shafts



Shafts — for use with OH selector handles .24 x .24" (6x6 mm)

Shaft length (in/mm)	Maximum mounting depth (inches)	Weight (Lbs.)	Catalog number	List price
5.1 / 130	5.6	0.08	OXS6X130	\$ 6
7.1 / 180	6.1	0.11	OXS6X180	6
9.8 / 250	10.3	0.13	OXS6X250	12
13 / 330	13.4	0.17	OXS6X330	20

NOTE: Selector handles and shafts are not recommended for use with fusible switches over 30A

Shafts — for use with pistol handles .24 x .24" (6x6 mm)

Shaft length (in/mm)	Maximum mounting depth (inches)				Weight (Lbs.)	Catalog number	List price
	OS30	OS60	OS100	OS200			
5.9 / 150	8.9	9.7	9.8	—	0.09	OXP6X150	\$ 12
8.3 / 210	9.7	12.1	12.2	9.9	0.13	OXP6X210	16
11.4 / 290	13.4	15.2	15.3	13.0	0.18	OXP6X290	20
14.2 / 360	18.7	12.9	18.0	—	0.23	OXP6X360	24
16.9 / 430	22.6	20.6	20.7	—	0.27	OXP6X430	28

Shafts — for use with pistol handles .47 x .47" (12x12 mm)

Shaft length (in/mm)	Maximum mounting depth (inches)		Weight (Lbs.)	Catalog number	List price
	OS400	OS600, OES800			
11.0 / 280	13.8	14.9	0.77	OXP12X280	\$ 36
12.8 / 325	15.6	16.7	0.9	OXP12X325	40
15.6 / 395	18.3	19.4	1.1	OXP12X395	44
18.3 / 465	21.0	22.1	1.32	OXP12X465	48
21.1 / 535	23.8	24.8	1.54	OXP12X535	52

① Mounting depth is distance from the outside of the door to the disconnect switch mounting plate. Shaft can be cut to desired length.