Number of contacts

2

Identification	Part number Male insert (M)	Part number Female insert (F)	Drawing	Dimensions in mm
Crimp terminal	**09 14 002 3001**	**09 14 002 3101**	 M F Contact arrangement view from termination side	

Identification	Wire gauge (mm²)	Part number Male contact	Part number Female contact	Drawing	Dimensions in mm
Han® D Coax contact 1 + shielding, 75 Ω Han D® crimp contacts		**09 15 001 3013**	**09 15 001 3113**	 M F	
Han D® Crimp contact gold plated	0.14-0.37	**09 15 000 6124**	**09 15 000 6224**		
	0.5	**09 15 000 6123**	**09 15 000 6223**		
	0.75	**09 15 000 6125**	**09 15 000 6225**		
	1	**09 15 000 6122**	**09 15 000 6222**		
	1.5	**09 15 000 6121**	**09 15 000 6221**		
	2.5	**09 15 000 6126**	**09 15 000 6226**		
Han® E Coax contact 1 + shielding, 50 Ω Han E® crimp contacts		**09 15 001 3023**	**09 15 001 3123**	 M F	
Han E® contacts gold plated 	0.14-0.37	09 33 000 6117	09 33 000 6217		
	0.5	**09 33 000 6122**	**09 33 000 6222**		
	0.75	**09 33 000 6115**	**09 33 000 6215**		
	1	**09 33 000 6118**	**09 33 000 6218**		
	1.5	**09 33 000 6116**	**09 33 000 6216**		
	2.5	**09 33 000 6123**	**09 33 000 6223**		
	4	09 33 000 6119	09 33 000 6221		
	5.5	**09 33 000 6139**	**09 33 000 6239**		

Order crimp contacts separately

Stock items in bold type