

Han® 3 A RJ45 Hybrid



Han® 3 A RJ45, Hybrid

Identification	Part No.	Drawing	Dimensions in mm
<p>Connector, Cat. 5, 4 + 4-poles (IDC termination for RJ45 insert)</p> <p>Plastic version, black</p>	09 45 125 1300		
<p>Metal version Standard, grey</p>	10 12 005 2001		
<p>Connector, Cat. 6, 8 + 4-poles (IDC termination for RJ45 insert)</p> <p>Plastic version, black</p>	09 45 125 1760		
<p>Metal version Standard, grey</p>	09 45 115 1760		
<p>Connector insert for Han® 3 A housings</p>	09 45 100 1760		
<p>New Cat. 6_A version with piercing connection AWG 28/7 - 24/7 (available Q3/2012)</p>	09 45 100 1720		
<p>Protection cover for connector IP 65 / IP 67 without seal</p> <p>Plastic version, black</p>	09 20 003 5442		
<p>Metal version Standard, grey</p>	09 20 003 5422		
<p>Metal version M</p>	09 37 003 5402		

Dimensions valid for plastic version