



Han® 3 A RJ45 10G Cat. 6 – panel feed throughs

## Advantages

- Compact and robust design
- 360° shielding
- Easy mounting
- Transmission category 6, performance class E<sub>A</sub>, suitable for 1/10 Gigabit Ethernet
- RJ45 mating compatible
- Coding (4 variants) possible

## Technical characteristics

Number of ports	2 / 1x Han® 3 A RJ45 (IP 65 / IP 67) 1x RJ45 (IP 20)
Transmission performance	Category 6 / class E <sub>A</sub> acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100 Mbit/s and 1/10 Gbit/s
Shielding	Fully shielded, 360° shielding contact
Mounting	Screwable to cover plates
Degree of protection	IP 65 / IP 67
Mating cycles	min. 500
Temperature range	-40 °C ... + 70 °C
Housing material	
Plastic version	Polycarbonate, black, UL 94 V-0
Metal version	Zinc die-cast, powder-coated

### Identification

### Part number

### Drawing

### Dimensions in mm

#### Panel feed-through set, 8-poles

- Plastic version, black
- Metal version Standard, grey
- Metal version M, black

09 45 225 1560  
09 45 215 1560  
09 45 215 1561

Metal version Standard, grey,  
with self-closing protective cap

09 45 215 1562

#### Han® 3 A RJ45 10G insert Cat. 6

(for Han® 3 A housings)

09 45 200 1560

#### Han® 3 A RJ45 HIFF adapter

to mount HIFF inserts (e.g. HARTING RJ Industrial® 10G RJ45 bulkhead or Ha-VIS preLink® RJ45) in Han® 3 A housings

09 45 515 0024

