

Identification	Part No.	Drawing	Dimensions in mm
<b>Transport protection</b> for device side IP 40	09 45 845 0003		max. 16.5 13.3 16.05 max. 19.3 max. 10
<b>Protection cover</b> for device side IP 65 / IP 67			
Version with passive locking without cord	09 45 845 0009 024		32.3 maxi IP67 easy dust cap 17.65 maxi 18 maxi
Version with passive locking with plastic cord for fixing screw M3	09 45 845 0009		(25) 180 13 Hole for M3 screw for panel fixing Ø3.1 Ø4.5
Version with passive locking with nylon cord for fixing screw M2.5 / M3	09 45 845 0011 024		120 Ø1.4 Ø3.2 Ø5
Version with active locking without cord	09 45 845 0015		36 20.2 maxi 70.7 maxi
Version with active locking with plastic cord for fixing screw M3	09 45 845 0014		(25) 180 13 Hole for M3 screw for panel fixing Ø3.1 Ø4.5
Version with active locking with nylon cord for fixing screw M2.5 / M3	09 45 845 0013		120 1 maxi Ø1.4 Ø3.2 Ø5
<b>Protection cover</b> for connectors IP 65 / IP 67	09 45 845 0010		150 1130 115 Clips hole 2 finger clips 48 max
<b>Security clip</b> for connectors can be sealed and protects against unauthorized unplugging	09 45 845 0020		16.5 maxi 13.5 maxi 1.46

PushPull