

Metal hoods/housings for industrial applications / 2 lever locking system

Identification	Image	Part number		Cable entry metric	Drawing	Dimensions in mm
		Low construction	High construction			
Hoods side entry		19 20 032 1521		1 x 25		82, 56, 60
Hoods side entry			19 20 032 0527	1 x 32		82, 56, 79
Hoods top entry			19 20 032 0426 19 20 032 0427	1 x 25 1 x 32		82, 56, 79
Dust protection cover		09 20 032 5401	09 20 032 5401			57.3, 67, 83.3, 16.5

Metal hoods/housings for industrial applications / 2 lever locking system

Identification	Image	Part number		Cable entry metric	Drawing	Dimensions in mm
		Low construction	High construction			
Housings, bulkhead mounting		09 20 032 0301				45, 10, 92, 102, 73, 48, 92, 42, 69, 29, 42, 56, 64.4
Housings, surface mounting side entry			19 20 032 0231 19 20 032 0232 19 20 032 0272	1 x 25 1 x 32 2 x 32		82, 94, 106, 8, 46, 57, 69, 4, 5.5, 10

Han Hoods Housings

Panel cut out

Blind way for one cable entry

* usable for two inserts of size 16 A
Stock items in bold type