



Ethernet Switch

Ha-VIS eCon 7100-AA

10-port Ethernet Switch for use in harsh industrial environments,
with 2 Gigabit ports

Unmanaged

IP 65 / IP 67

PROFINET compatible



EtherNet/IP compatible



Number of ports, Copper / Termination

8x 10/100Base-T(X) / Han® 3 A RJ45 (female)
2x 10/100/1000-Base-T(X) / Han® 3 A RJ45 (female)

Input voltage / Termination

24 / 48 V DC / Han® 4 A, male, for redundant power supply

Permissible range (min./max.)

12 V ... 60 V DC

Input current

approx. 230 mA (at 24 V DC)

Alarm signalling contact

Change-over contact, potential-free, 24 V DC / 0.5 A
Han® 3 A, male

Housing material

zinc die-cast

Dimensions (W x H x D)

90 x 120 x 87 mm

Weight

approx. 1,4 kg

Working temperature

-40 °C ... +70 °C

eCon 7000

Identification

Part number

Drawing

Dimensions in mm

Ha-VIS eCon 7100-AA

Ethernet Switch with
10 ports M12 D-coding

20 70 310 3924

