



Ethernet Switch
Ha-VIS eCon 4080-B1
8-port Ethernet Switch for flat wall mounting

Unmanaged	IP 40	PROFINET comatible ☒	EtherNet/IP compatible ☒
-----------	-------	--	--

Number of ports, Copper / Termination	8x 10/100Base-T(X) / M12 D-coding
Input voltage / Termination	24 / 48 V DC / M12 A-coding, male, for redundant power supply
Permissible range (min./max.)	12 V ... 60 V DC
Input current	approx. 150 mA (at 24 V DC)
Housing material	metal, powder-coated
Dimensions (W x H x D)	130 x 166 x 50 mm (without connectors)
Weight	approx. 0,85 kg
Working temperature	-40 °C ... +70 °C
Approvals	e1
MTBF	1.544.000 h

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Ha-VIS eCon 4080-B1 Ethernet Switch with 8 ports M12 D-coding for wall mounting	20 77 208 3001		
--	----------------	--	--