



Ethernet Switch

Ha-VIS mCon 4080-B1V

8-port Ethernet Switch for flat installation

Managed	IP 40	PROFINET comatible ☒	EtherNet/IP compatible ☒
Number of ports, Copper / Termination	8x 10/100Base-T(X) / M12 D-coding (female)		
Input voltage / Termination	24 / 48 V DC / M12 A-coding, male, for redundant power supply		
Permissible range (min./max.)	12 V ... 60 V DC		
Input current	approx. 165 mA (at 24 V DC)		
Housing material	metal, powder-coated		
Dimensions (W x H x D)	130 x 166 x 50 mm (without connectors)		
Weight	approx. 0.85 kg		
Working temperature	-40 °C ... +70 °C		
Approvals			
MTBF	489.000 h		
Management	fully managed via Web interface and SNMP Functions see page A·9		
Identification	Part number	Drawing	Dimensions in mm
Ha-VIS mCon 4080-B1V Ethernet Switch with 8 ports M12 D-coding for wall mounting	20 77 208 4001		