


Product information

RKC 30 - RKC 50 - RKC 50/9


Industrial Connecting Solutions: Circular Connectors: 7/8", M23 Connectors: 7/8" Connectors: Field Attachable 7/8" Connectors: Female Connectors: RKC 30 - RKC 50

http://e-catalog.hirschmann.com/link/57078-24228-256281-256289-256290-276563-276566-248843/en/RKC_05-09/uistate

Name	RKC 30 - RKC 50
	
	Field attachable connector, 7/8" female connector, straight version, with threaded joint, assembling with screw terminals, 5 poles, screwed cable gland with PG 9 thread.
Delivery informations	
Availability	available
Product description	
Type	RKC 50/9
Order No.	11225
Description	Field attachable connector, 7/8" female connector, straight version, with threaded joint, assembling with screw terminals, 5 poles, screwed cable gland with PG 9 thread.
Number of contacts	5
Color of housing	black
Product characteristics	Oil resistance
Mechanical data	
Type of plug-in contact	Female connector
Design of housing	straight
Thread	7/8"
Design of electrical connection	screw connection
LED display present	✘
Screw joint for cable for external cable diameter	6.0 mm ... 8.0 mm
Screwed cable gland, connecting thread	Pg9
Environmental conditions	
Environmental temperature	-40 °C ... 90 °C
Degree of protection (IP), mounted	IP67
Pollution degree	3
Materials	
Housing material / Molded body	PA
Contact bearer material	TPU, self-extinguishing
Contact material	CuZn
Contact material - Surface refinement	silver-plated and gold-plated
Knurled screw / nut material	Al anodized
Sealing material	NBR
Electrical data	
Contact resistance	≤ 5 mΩ
Rated current In	at 40 °C, UL and notice derating, 9 A
Nominal voltage	240 V
Rated voltage	250 V
Test voltage	1.5 kV eff./60 s
Insulation resistance	> 10 GΩ
Approvals	
Approvals	UL
RoHS 2002/95/EG compliant	RoHS 2002/95/EG

Picture

Drawing



*is left oder schraubendrehen als
Montagehilfe
and an screwdriver as
assembly tool
*is left
*is left
*is left

Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.