

Product information N6R FM R

http://www.e-catalog.beldensolutions.com/link/	
Name	NGR FM R
	Angled cable plug with knurled screw, strain relief by means of a clamping cage
Delivery informations	
Availability	available
Product description	
Description	Angled cable plug with knurled screw,
	strain relief by means of a clamping cage
Туре	NGR FM R
Order No.	931 727-106
Type of contact	male
Number of contacts	6 + PE
Cable gland	PG 11
Cable diameter	7 mm to 9 mm
Conductor size	max. 1.5 mm ²
Standard	DIN 43651
Housing Color	ÖleÀ
Technical data	
Pin dimensions	1.6 mm
Rated voltage	AC/DC 250 V
Rated current	10 A
Contact resistance	<= 5 m0hm
Type of termination	crimp
Suitable cables	0.5 mm ² to 1.5 mm ²
Material	
Contact surface material	Ag
Contact bearer material	PET
Housing material	PET
Environmental conditions	
Protection class (IEC 60529)	IP 65
Temperature range	-40 °C to +90 °C
Packing unit	
Packaging unit	10 pieces
Scope of delivery and accessories	
Scope of delivery	1 cable plug, with knurled screw, not assembled, in polythene, with assembly instructions
Accessories to order separately	can be plugged into NGR AF, NGR BFE, NGR DM; coding NC 6, order no. 831 002-011 contacts: RSC 162







Industrial Connecting Solutions:Circular Connectors:MIL, DIN, Universal Connectors (NR series):Cable plug:N6R FM R http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256284-24367-24371-36239/en/conf/uistate Picture Drawing

Belden Deutschland GmbH

Im Gewerbepark 2 58579 Schalksmühle Germany Phone: +49 7127/14-1806 E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.



