




Product information N6R BM FA

Industrial Connecting Solutions: Circular Connectors: MIL, DIN, Universal Connectors: DIN 43651 Connectors (NR series): Surface mounted connector: N6R BM FA

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256284-24367-24373-36310/en/conf/ui/state>

Name	N6R BM FA
	
	Surface-mounted connector with flange
Delivery informations	
Availability	available
Product description	
Description	Surface-mounted connector with flange
Type	N6R BM FA
Order No.	932 437-206
Type of contact	male
Number of contacts	6 + PE
Conductor size	max. 1.5 mm ²
Housing Color	grey
Technical data	
Pin dimensions	1.6 mm
Rated voltage	AC/DC 250 V
Rated current	10 A
Contact resistance	<= 5 mOhm
Type of termination	crimp
Suitable cables	0.5 mm ² to 1.5 mm ²
Mounting	flange
Material	
Contact surface material	Ag
Contact bearer material	PET
Housing material	PET
Environmental conditions	
Protection class (IEC 60529)	IP 65
Temperature range	-40 °C to +90 °C
Packing unit	
Packaging unit	10 pieces
Scope of delivery and accessories	
Scope of delivery	1 surface-mounted connector with flat gasket, not assembled, in polythene bag with assembly instructions
Accessories to order separately	can be plugged into N6R FF, N6R FF R, N6R EF, N6R FF S 11; coding NC 6, order no. 831 002-011 protective cover SHK 2, order no. 733 845-001, contacts: RSC 162

