




# HIRSCHMANN

A BELDEN BRAND

## Product information N11R AM 5

Industrial Connecting Solutions: Circular Connectors: MIL, DIN, Universal Connectors: DIN 43651 Connectors (NR series): Panel-mounted connector: N11R AM 5

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256284-24367-24372-36306/en/conf/ui/state>

Name		N11R AM 5
		
		Panel-mounted connector with metal screw-in casing (metall segment)
<b>Delivery informations</b>		
Availability		available
<b>Product description</b>		
Description		Panel-mounted connector with metal screw-in casing (metall segment)
Type		N11R AM 5
Order No.		932 627-106
Type of contact		male
Number of contacts		11 + PE
Conductor size		max. 0.5 mm <sup>2</sup>
Standard		DIN 43651
Housing Color		grey
<b>Technical data</b>		
Pin dimensions		1.6 mm
Rated voltage		AC/DC 60 V
Rated current		5 A
Contact resistance		<= 5 mOhm
Type of termination		crimp
Suitable cables		0.14 mm <sup>2</sup> to 0.5 mm <sup>2</sup>
Mounting		PG 13,5
<b>Material</b>		
Contact surface material		Ag
Contact bearer material		PET
Housing material		PET
<b>Environmental conditions</b>		
Protection class (IEC 60529)		IP 65
Temperature range		-40 °C to +90 °C
<b>Packing unit</b>		
Packaging unit		10 pieces
<b>Scope of delivery and accessories</b>		
Scope of delivery		1 panel-mounted connector, not assembled, in polythene bag with assembly instructions
Accessories to order separately		can be plugged into N11R FF, N11R EF; protective cover SHK 2, order no. 733 845-001 contacts: RSC 162/1

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256284-24367-24372-36306/en/conf/uistate>

### Picture

## Drawing



Im Gewerbepark 2  
58579 Schalksmühle  
Germany  
Phone: +49 7127/14-1806  
E-Mail: [icos-sales@belden.com](mailto:icos-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.