



## Product information GSR-U 3000 LO schwarz/black

Industrial Connecting Solutions:Rectangular Connectors:Valve Connectors (Type A -B -C):Type A:Receptacle Valve Connectors (DIN EN 175 301-803):GSR-U 3000 LO schwarz/black

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256270-276216-35182/en/conf/ulistate>

Name GSR-U 3000 LO schwarz/black



appliance connector for injection molding (IP 65 unmated) with solder lug for flexible cables

### Delivery informations

Availability available

### Product description

Description appliance connector for injection molding (IP 65 unmated) with solder lug for flexible cables

Type GSR-U 3000 LO schwarz/black

Order No. 933 376-100

Number of contacts 3 + PE

Standard DIN EN 175 301-803-A

Housing Color black

Construction type A

### Technical data

Rated voltage AC/DC 400 V

Rated current 16 A

Contact resistance  $\leq 4 \text{ m}\Omega$

Type of termination solder

Mounting for molding

### Material

Contact surface material Sn

Contact bearer material PA

Housing material PA

### Environmental conditions

Protection class (IEC 60529) IP 65 (gasket necessary)

Pollution severity 3

Temperature range  $-40 \text{ }^\circ\text{C}$  to  $+125 \text{ }^\circ\text{C}$

### Inflammability class

Contact bearer 94 V-0

### Approvals


UR UR

### Packing unit

Packaging unit 200 pieces

### Picture

Drawing





**HIRSCHMANN**

A **BELDEN** BRAND

**Belden Deutschland GmbH**

Im Gewerbepark 2

58579 Schalksmühle

Germany

Phone: +49 7127/14-1806

E-Mail: [icos-sales@belden.com](mailto:icos-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.