




## Product information EF12LW4 Au

Industrial Connecting Solutions:Archive - Industrial Connectors:Circular Connectors E-series M12 / M12 push-pull (Archive):with screw locking:Appliance socket for front panel mounting (circuit board):EF12LW4 Au

<http://www.e-catalog.beldensolutions.com/link/57078-24228-62529-24256-24257-24274-38215/en/conf/uistate>

|  |   |
|--|---|
| Name                                     | EF12LW4 Au  |
|  |                                      |
|  | Horizontal appliance socket for combined front panels and circuit board installation with 2 metal screws, 2 x O-rings |
| <b>Delivery informations</b>             |   |
| Availability                             | no longer available   |
| <b>Product description</b>               |   |
| Description                              | Horizontal appliance socket for combined front panels and circuit board installation with 2 metal screws, 2 x O-rings |
| Type                                     | EF12LW4 Au  |
| Order No.                                | 933 395-200   |
| Type of contact                          | female  |
| Number of contacts                       | 4   |
| Standard                                 | IEC 61076-2-101 (Ed. 1)/ IEC 60947-5-2  |
| Housing Color                            | metallic  |
| <b>Technical data</b>                    |   |
| Rated voltage                            | AC/DC 150 V   |
| Rated current                            | 4 A   |
| Type of termination                      | solder, solid pins diameter 1 mm  |
| <b>Material</b>                          |   |
| Contact material                         | Cu Zn   |
| Contact surface material                 | Au  |
| Contact bearer material                  | PA  |
| Housing material                         | Cu Zn/Ni  |
| O-Ring                                   | NBR   |
| <b>Environmental conditions</b>          |   |
| Protection class (IEC 60529)             | IP 68   |
| Pollution severity                       | 3   |
| Temperature range                        | -25 °C to +90 °C  |
| <b>Inflammability class</b>              |   |
| Contact bearer                           | 94 V-2  |
| <b>Approvals</b>                         |   |
| UL                                       | UL pending  |
| <b>Packing unit</b>                      |   |
| Packaging unit                           | 100 pieces  |
| <b>Scope of delivery and accessories</b> |   |
| Accessories to order separately          | protective cap M12 VS,<br>order no. 734 209-100   |



**HIRSCHMANN**

A **BELDEN** BRAND

58579 Schalksmühle

Germany

Phone: +49 7127/14-1806

E-Mail: [icos-sales@belden.com](mailto:icos-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.