




Product information EF12L OCTOPUS


Industrial Connecting Solutions:Circular Connectors:M8 - M12 Connectors:M12 Connectors:Bus connectors:Connecting technology:EF12L OCTOPUS

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256292-256304-24292-24293-39125/en/conf/ui/state>

Name	EF12L OCTOPUS
	
	Industrial ETHERNET M12 socket, "D"-coded according IEC 61076-2-101 for combined front panels and circuit board installation
Delivery informations	
Availability	available
Product description	
Description	Industrial ETHERNET M12 socket, "D"-coded according IEC 61076-2-101 for combined front panels and circuit board installation
Type	EF12L OCTOPUS
Order No.	934 451-021
Type of contact	female
Number of contacts	4
Data rate	10BASE-T, 100BASE-TX
Standard	IEC 61076-2-101
Housing Color	metallic
Technical data	
Rated voltage	AC/DC 150 V
Rated current	4 A (Derating)
Type of termination	soldering, straight pins
Material	
Contact material	Cu Zn
Contact surface material	Au
Contact bearer material	PA
Housing material	Cu Zn/Ni
O-Ring	Viton
Environmental conditions	
Protection class (IEC 60529)	IP 67 / IP65
Pollution severity	3
Temperature range	-25 °C to +90 °C
Approvals	
UL	UL
Packing unit	
Packaging unit	25
Scope of delivery and accessories	
Accessories to order separately	protective cap M 12 VS, order no. 734 209-100 M12 connector EM12S OCTOPUS, order no. 934 445-001 patchcords EM12S 001Lxxxx OCTOPUS, order no. 934 497-xxx

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.