

Product information

BAT-ANT-N-14G

Industrial Ethernet:Archive - Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-14G

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49814-49859-24498-24499-40453/en/conf/uistate>

Name	
BAT-ANT-N-14G	
	
directional antenna for 2.4 GHz	
Delivery informations	
Availability	no longer available
Product description	
Description	directional antenna for 2.4 GHz
Type	BAT-ANT-N-14G
Order No.	943 903 380
Cable length	1 m
Cable specification	2 N male connectors; 1.0 dB at 2.4 GHz
Radio technology	
Range	siehe Antennen-Kalkulator auf www.hirschmann-ac.de
Frequency band	2300 MHz - 2500 MHz
Polarisation	linear, vertical
Elevation, Azimuth	30°
VSWR	1.5
Gain	14 dBi
Antenna connector	N female
Ambient conditions	
Operating temperature	-40 °C to +80 °C
Storage/transport temperature	-40 °C to +80 °C
Wind load	57 N at 160 km/h
Mechanical construction	
Dimensions (W x H x D)	200 mm x 200 mm x 43 mm
Mounting	wall, mast
Protection class	IP55
Material	ASA
Weight	0.5 kg
Scope of delivery and accessories	
Scope of delivery	antenna, cable 1m N to N, installation material

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.