




Product information BAT-ANT-N-14G-IP23

Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-14G-IP23

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49859-24498-24499-65479/en/conf/uistate>

Name	BAT-ANT-N-14G-IP23
	
	Directional antenna for 2.4 GHz with 14 dBi gain
Delivery informations	
Availability	available
Product description	
Description	Directional antenna for 2.4 GHz with 14 dBi gain
Type	BAT-ANT-N-14G-IP23
Order No.	943 981-005
Cable length	1 m
Cable specification	N-plug to N-plug
Radio technology	
Range	Please use the antenna distance calculator.
Frequency band	2400 - 2500 MHz
Polarisation	linear, vertical
Elevation, Azimuth	30°
VSWR	2
Gain	14 dBi
Antenna connector	N female
Ambient conditions	
Operating temperature	-40 °C to +80 °C
Storage/transport temperature	-40 °C to +80 °C
Wind load	10 N at 160 km/h
Mechanical construction	
Dimensions (W x H x D)	n/a
Mounting	wall, mast
Protection class	IP23
Material	plastic
Weight	0.3 kg
Scope of delivery and accessories	
Scope of delivery	antenna, 1m cable, pigtail, mounting material

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.