




Product information BAT-ANT-N-5A-IP65

Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-5A-IP65

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49859-24498-24499-64578/en/conf/uistate>

Name	BAT-ANT-N-5A-IP65
	
	Omnidirectional antenna for 5 GHz band
Delivery informations	
Availability	available
Product description	
Description	Omnidirectional antenna for 5 GHz band
Type	BAT-ANT-N-5A-IP65
Order No.	943 981-003
Cable length	1 m
Cable specification	N-plug to N-plug
Radio technology	
Range	refer to antenna distance calculator
Frequency band	5150 - 5875 MHz
Polarisation	linear, vertical
Elevation, Azimuth	vertical: 25°, horizontal: 360°
VSWR	1.5
Gain	5 dBi
Antenna connector	N female, DC grounded
Ambient conditions	
Operating temperature	-45 °C to +70 °C
Storage/transport temperature	-45 °C to +70 °C
Mechanical construction	
Dimensions (W x H x D)	16 x 160 mm
Mounting	wall, mast
Protection class	IP65
Material	Polypropylen
Weight	0.3 kg
Scope of delivery and accessories	
Scope of delivery	antenna, 1 m cable, pigtail, mounting material

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.