




## Product information BAT-ANT-N-6G-IP65

Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-6G-IP65

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49859-24498-24499-64628/en/conf/uistate>

Name	BAT-ANT-N-6G-IP65
	
	Omnidirectional antenna for 2.4 GHz band
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	Omnidirectional antenna for 2.4 GHz band
Type	BAT-ANT-N-6G-IP65
Order No.	943 981-002
Cable length	1 m
Cable specification	N-plug to N-plug
<b>Radio technology</b>	
Range	refer to antenna distance calculator
Frequency band	2400 - 2500 MHz
Polarisation	linear, vertical
Elevation, Azimuth	360°, 0° downtilt
VSWR	1.8
Gain	6 dBi
Antenna connector	N female, DC grounded
<b>Ambient conditions</b>	
Operating temperature	-40 °C to +80 °C
Storage/transport temperature	-40 °C to +80 °C
<b>Mechanical construction</b>	
Dimensions (W x H x D)	Ø 22 x 250 mm
Mounting	wall, mast
Protection class	IP65
Material	fiber glass
Weight	0.3 kg
<b>Scope of delivery and accessories</b>	
Scope of delivery	antenna, 1 m cable, pigtail, mounting material

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.