




Product information BAT-ANT-N-8G-DS-IP65

Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-8G-DS-IP65

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49859-24498-24499-65278/en/conf/uistate>

Name	BAT-ANT-N-8G-DS-IP65
	
	directional diversity antenna linear for 2.4 GHz
Delivery informations	
Availability	available
Product description	
Description	directional diversity antenna linear for 2.4 GHz
Type	BAT-ANT-N-8G-DS-IP65
Order No.	943 981-009
Cable length	1 m
Cable specification	N male to N male
Radio technology	
Range	Please refer to the Antenna Distance Calculator.
Frequency band	2300 MHz - 2500 MHz
Polarisation	dual linear, +/- 45° slant
Elevation, Azimuth	3 dB beam width 70° / 80°
VSWR	1.5
Gain	8.5 dBi
Antenna connector	N female
Ambient conditions	
Operating temperature	-40 °C to +80 °C
Storage/transport temperature	-40 °C to +80 °C
Wind load	15 N at 160 km/h
Mechanical construction	
Dimensions (W x H x D)	101 mm x 95 mm x 32 mm
Mounting	wall, mast
Protection class	IP65
Material	LEXAN EXL 9330
Weight	0.11 kg
Scope of delivery and accessories	
Scope of delivery	antenna, 2x 1 m cable, mounting material, 2x Pigtail N to RP-SMA

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.