


Product information

BAT-ANT-N-MiMoDB-5N-IP65

Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-MiMoDB-5N-IP65

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49859-24498-24499-65329/en/conf/ui/state>

Name	
BAT-ANT-N-MiMoDB-5N-IP65	
	
directional diversity antenna linear for 2.4 GHz and 5 GHz.	
Delivery informations	
Availability	available
Product description	
Description	directional diversity antenna linear for 2.4 GHz and 5 GHz.
Type	BAT-ANT-N-MiMoDB-5N-IP65
Order No.	943 981-012
Cable length	3x 90 cm directly mounted
Cable specification	N plug
Radio technology	
Range	refer to antenna distance calculator
Frequency band	2400-2500 / 5150-5875
Polarisation	triple linear, vertical
Elevation, Azimuth	horizontal 360°
VSWR	1.8
Gain	3,5 dBi / 5,5 dBi
Antenna connector	N plug
Ambient conditions	
Operating temperature	-40 °C to +80 °C
Storage/transport temperature	-40 °C to +80 °C
Wind load	15 N at 160 km/h
Mechanical construction	
Dimensions (W x H x D)	310 mm x 110 mm x 40 mm
Mounting	ceiling, wall
Protection class	IP65
Material	plastic
Weight	0.11 kg
Scope of delivery and accessories	
Scope of delivery	antenna, 3x pigtail N to RP-SMA, mounting material

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.