




Product information BAT-Controller WLC25

Industrial Ethernet:Industrial Wireless LAN:Chassis:BAT-Management:BAT-Controller WLC25

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49859-24497-118024-144719/en/conf/uistate>

Name	BAT-Controller WLC25
	
	Central Firmware deployment and management of the Access Points. Requires an external web server.
Delivery informations	
Availability	available
Product description	
Description	Central Firmware deployment and management of the Access Points. Requires an external web server.
Port type and quantity	4 individual Ethernet ports 10/100/1000 Mbps
Type	BAT-Controller WLC25
Order No.	942 034-001
Managed Access Points	25
More Interfaces	
Power supply/signaling contact	Internal power supply unit (110–230 V, 50-60 Hz)
Hardware requirements	
Network	BAT54 and BAT300 access points
Mechanical construction	
Housing	Robust metal housing, 19" 1 HU, with removable mounting brackets, network connectors on the front
Ambient conditions	
Operating temperature	5 °C ... 40 °C
Relative humidity (non-condensing)	0 % ... 95 %
Dimensions (W x H x D)	435 x 45 x 207 mm
Weight	3800 g
Scope of delivery and accessories	
Scope of delivery	CD including firmware, management software (LANconfig, LANmonitor, WLANmonitor) and documentation. Printed Installation Guide. 1 serial configuration cable (1.5 m), 1 Ethernet cable, 1 Cable IEC power cord (3 m), return voucher, 19 Inch DIN rail adapter

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.

