


Product information

M4-GIGA 8-SFP

Industrial Ethernet:Backbone Switches:Media modules:M4-GIGA 8-SFP

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49838-24527-40328/en/conf/ui/state>

Name	
M4-GIGA 8-SFP	
	
Media module for MACH 4000 1000BASE-X with SFP sockets (nicht MACH4002-48+4G)	
Delivery informations	
Availability	available
Product description	
Description	Media module for MACH 4000 1000BASE-X with SFP sockets (nicht MACH4002-48+4G)
Port type and quantity	8 x 100/1000 BASE-X using M-FAST SFP (100MBit/s) or M-SFP (1000MBit/s) transceiver
Type	M4-GIGA 8-SFP
Order No.	943 879-001
Service	
Diagnostics	LEDs (power, link status, data, full duplex, ring port, LED test)
Technical data	
Operating voltage	power supply via the backplane of the MACH 4000 switches
Operating temperature	0°C to +60°C
Power consumption	15 W
Approvals	
Safety of industrial control equipment	cUL 508
Safety of information technology equipment	cUL 60950-1
Shipbuilding	Germanischer Lloyd

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.