


## Product information

### M4-P-24VDC 300W

Industrial Ethernet:Backbone Switches:Power supplies:M4-P-24VDC 300W

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49838-24531-39839/en/conf/ui/state>

Name	
M4-P-24VDC 300W	
	
Power supply for M4-Power chassis with two inputs for redundant power supply	
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	Power supply for M4-Power chassis with two inputs for redundant power supply
Order No.	943 876-001
Type	M4-P-24VDC 300W
<b>Service</b>	
Diagnostics	LEDs (P3 und P4) at basic device
<b>Technical data</b>	
Operating voltage	24 V DC (19,2 V - 32 V)
Operating temperature	0°C to +60°C
Nominal power of voltage supply	380 W
<b>Power requirements</b>	
Current consumption	max. 21 A (24 V DC)
<b>More Interfaces</b>	
Voltage input	plug-in terminal block
<b>Approvals</b>	
Safety of industrial control equipment	cUL 508
Safety of information technology equipment	cUL 60950-1
Shipbuilding	Germanischer Lloyd
<b>Scope of delivery and accessories</b>	
Scope of delivery	device, power-cable 1m (M4-POWER to Switch)

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.

