


Product information

M4-P-48VDC 300W

Industrial Ethernet:Backbone Switches:Power supplies:M4-P-48VDC 300W

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49838-24531-39840/en/conf/ui/state>

Name	
M4-P-48VDC 300W	
	
Power supply for M4-Power chassis with two inputs for redundant power supply	
Delivery informations	
Availability	available
Product description	
Description	Power supply for M4-Power chassis with two inputs for redundant power supply
Order No.	943 877-001
Type	M4-P-48VDC 300W
Service	
Diagnostics	LEDs (P3 und P4) at basic device
Technical data	
Operating voltage	48 V DC (38 V - 72 V)
Operating temperature	0°C to +60°C
Nominal power of voltage supply	350 W
Power requirements	
Current consumption	max. 10,1 A (48 V DC)
More Interfaces	
Voltage input	plug-in terminal block
Approvals	
Safety of industrial control equipment	cUL 508
Safety of information technology equipment	cUL 60950-1
Shipbuilding	Germanischer Lloyd
Scope of delivery and accessories	
Scope of delivery	device, power-cable 1m (M4-POWER to Switch)

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.

