


Product information

M4-S-24VDC 300W

Industrial Ethernet:Backbone Switches:Power supplies:M4-S-24VDC 300W

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49838-24531-39842/en/conf/uistate>

Name	M4-S-24VDC 300W
	
	Power supply for MACH 4002 chassis with two inputs for redundant power supply
Delivery informations	
Availability	available
Product description	
Description	Power supply for MACH 4002 chassis with two inputs for redundant power supply
Order No.	943 871-001
Type	M4-S-24VDC 300W
Service	
Diagnostics	LEDs (P1 und P2) at basic device
Technical data	
Operating voltage	24 V DC (19,2 V - 32 V)
Operating temperature	0°C to +60°C
Nominal power of voltage supply	380 W
Power requirements	
Current consumption	max. 21 A (24 V DC)
More Interfaces	
Voltage input	plug-in terminal block
Approvals	
Safety of industrial control equipment	cUL 508
Safety of information technology equipment	cUL 60950-1
Shipbuilding	Germanischer Lloyd
Scope of delivery and accessories	
Scope of delivery	device, manual

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.

