




Product information M4-S-AC/DC 300W

Industrial Ethernet:Backbone Switches:Power supplies:M4-S-AC/DC 300W

<http://www.e-catalog.beldensolutions.com/link/57078-24455-49838-24531-39841/en/conf/ui/state>

Name	M4-S-AC/DC 300W
	
	Power supply for MACH 4002 switch chassis
Delivery informations	
Availability	available
Product description	
Description	Power supply for MACH 4002 switch chassis
Order No.	943 870-001
Type	M4-S-AC/DC 300W
Service	
Diagnostics	LEDs (P1) at basic device
Current consumption	
Activation current	typ. < 40 A at 265 V AC and cold start
Technical data	
Operating voltage	100-240 V AC
Operating temperature	0°C to +60°C
Input frequency	47-63 Hz
Nominal power of voltage supply	350 W (230 V), 370 W (110 V)
Power requirements	
Current consumption	1,8 A (230 V), 4,2 A (115V)
More interfaces	
Voltage input	Non-heating appliance socket
Approvals	
Safety of industrial control equipment	cUL 508
Safety of information technology equipment	cUL 60950-1
Shipbuilding	Germanischer Lloyd
Scope of delivery and accessories	
Scope of delivery	device, manual

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.