



T50R0HSUVM4

High Temp Tie, 8" Long, 50lb Tensile Strength, PA66HSUV, Black, 1000/pkg

Article Number: 111-04907

Part Number: T50R0HSUVM4

Type: T50R


Base Data

| | |
|--------------------------------------|--|
| Part No. | T50R0HSUVM4 |
| Type | T50R |
| Color | Black (BK) |
| Features | <ul style="list-style-type: none">• Heat and UV stabilized cable ties provide excellent resistance to high heat and UV exposures.• Inside serrations allow for strong hold on cables and wire bundles.• Head design provides high tensile strength with very low insertion force.• Bent tail ensures a quick and simple installation. |
| Application Method | Quick, simple fixing by hand or with HellermannTyton tensioning tools |
| Identification Plate Position | none |
| Releasable Closure (Yes/No) | No |
| Tie Closure | plastic pawl |
| Typical Application | Used to bundle and secure wire and cable. |
| Variant | Inside Serrated |

Product Dimensions

| | |
|------------------------------|------------------|
| Min. Tensile Strength | 50.0lbs / 225.0N |
| Length (L) | 8.0" / 202.0mm |
| Width (W) | 0.18" / 4.6mm |
| Min. Ø Bundle | 0.06" / 1.5mm |
| Max. Ø Bundle | 1.97" / 50.0mm |

Material and Specifications

| | |
|--------------------------------------|---|
| Material | Polyamide 6.6 heat and UV stabilized (PA66HSUV) |
| Flammability | UL94 V2 |
| Material Specification | RoHS |
| Operating Temperature | -40 °F to +257 °F, continuous |
| ROHS Conformity |  RoHS |
| UL Listed (US and Canada) | No |
| UL Recognized (US and Canada) | No |

Logistic and Packaging

| | |
|-----------------------|---------------|
| Packaging Type | bag |
| Pkg. Qty. | 1000 |
| Carton Qty. | 5000 |
| EAN code | 4031026311890 |
| UPC | 089306087144 |