



Combines Style  
and Economy  
3100 Series

3100MW5



Uncompromising performance. Bold design.

Raising the bar in guest room telephone performance and design.

Introducing Marquis® 3100 Series telephones by Telematrix.  
A bold new merger of design and engineering.



### Models

- ▶ Single line Non-Speakerphones
- ▶ Single and Two line Speakerphones

### Feature

- ▶ Professional quality speakerphone
- ▶ Conference (Recall) & Redial keys
- ▶ TouchLite® voice mail retrieval button technology on most models
- ▶ 10, 5 or 0 programmable guest service keys
- ▶ Convenient data port
- ▶ 5 Year "no hassle" warranty

### Colors

- ▶ Light Ash & Black
- ▶ Custom colors - minimum quantities apply

QUESTIONS: [info@telematrix.net](mailto:info@telematrix.net)  
SERVICE: [customerservice@telematrix.net](mailto:customerservice@telematrix.net)  
WEB SITE: [www.telematrix.net](http://www.telematrix.net)

## 3100 Series

### Features & Specifications:

**MARQUIS SERIES**

**3100 SERIES**  
Single and Two Line  
Telephones

#### Product Identification & Order Numbers:

##### Single Line Telephones

- ▶ Model No. 3100LBY - lobby phone  
P/N 31009 (light ash) / P/N 310091 (black)
- ▶ Model No. 3100MWB - basic phone  
P/N 31039 (light ash) / P/N 310391 (black)
- ▶ Model No. 3100MW5 - 5 memory keys, nonspeaker  
P/N 31139 (light ash) / P/N 311391 (black)
- ▶ Model No. 3100MW10 - 10 memory keys, nonspeaker  
P/N 31239 (light ash) / P/N 312391 (black)
- ▶ Model No. 3100MWD5 - 5 memory keys, speaker  
P/N 31149 (light ash) / P/N 311491 (black)
- ▶ Model No. 3100MWD - 10 memory keys, speaker  
P/N 31339 (light ash) / P/N 313391 (black)

##### Two Line Telephones:

- ▶ Model No. 3102MWD - 2-Line, 10 memory keys, speaker  
P/N 32359 (light ash) / P/N 323591 (black)
- ▶ Model No. 3102MWD5 - 2-Line, 5 memory keys, speaker  
P/N 32149 (light ash) / P/N 321491 (black)
- ▶ Model No. 3102MWS - 2-Line, No memory keys, speaker  
P/N 32049 (light ash) / P/N 320491 (black)
- ▶ Custom Colours available in minimum quantities  
of 500 or more for 'premium' colours.

#### Product Information:

- ▶ Installation Includes
  - RJ14 Line Cords - 15ft./4.5m
  - Handset Coil Cord - 9ft/2.25m
  - Optional Wall Mount Bracket (not included)
- ▶ Line, MW, and Ringer Specifications
  - Line Voltage 24-52VDC (+/-)
  - Line Current 20mA-100mA
  - Switchable for 90VDC Neon or Low Voltage  
LED Applications
  - Ringer Equivalence - 0.6B
- ▶ Unit Dimensions  
8.5"/21.5cm(l) 6.75"/17cm(w) 3.25"/8.5cm(h)
- ▶ Packaging Weight  
MasterPack Quantities of 10 Units, 31lbs/14.06kg
- ▶ Certifications  
FCC Part 68, FCC Part 15 & UL 1459 Ref.  
ADA/FCC Hearing Aid Compliant

#### Deluxe Features:

- ▶ Single and Two Line Telephones
- ▶ Compatible with PABX Systems
- ▶ Soft Key Technology
- ▶ Convenient Data Port
- ▶ SteelTrap® Memory Technology - no batteries required
- ▶ On-Hook Pre-Dialing on Memory Keys
  
- ▶ Turnkey Telephone Modifications Available - Ready for  
Instant Installation
- ▶ Full Length Custom Tailored Faceplates
- ▶ Industrial Grade Construction with Matte Finish Design
- ▶ Non-Slip Base

#### Audio/Visual Features:

- ▶ Exceptional Quality Speakerphone
- ▶ Large, Bright Red, TouchLite® Message Waiting Lamp
- ▶ 4 Step Speaker and Handset Volume Control  
(3-step on 3100MWB & 3100LBY models)
- ▶ High/Low Ringer Volume Switch
- ▶ Line Status LED Indication
- ▶ Speaker Key with On/Off Indication
- ▶ Mute Key with LED On/Off Indication
- ▶ Hold Key with LED On/Off Indication and Remote Release
- ▶ 3 Way Conference Calling Key (2 line models only)

#### Programming Features:

- ▶ TouchLite® Message Retrieval (programmable)  
(message light only on 3100MWB, no message light on 3100LBY)
- ▶ 10, 5 or No Guest Service Keys with Secure Programming
- ▶ Memory Key Entry - Maximum 32 Digits
- ▶ Flash Key (submerged) - 100 - 1000mS (programmable),  
600mS Timing (default), Storable
- ▶ Pause Key (submerged) - 1.0 - 5.0 Sec. (programmable),Storable
- ▶ Store Key (submerged)

