



DESIGNED FOR TIGHT SPACES  
AND TIGHTER BUDGETS.



Nugget 3

## THE TELEDEX NUGGET SERIES

Space-saving design. Money-saving value.



# TELEDEX NUGGET 3

# TELEDEX NUGGET

## Economical Guestroom Telephone with Data Port, Message Waiting and 3 Guest Service Buttons

- **Single Line Telephones**
- **ADA Handset Volume Boost** – Compliant with HAC/VC and FCC requirements
- **Data Port** – Easy access for laptop modem or fax machine use
- **Raised Red Message Waiting Lens** – Easily seen from any area in the guestroom
- **Paper Faceplate** – Allows user-friendly customization
- **Patented MultiX™ Message Waiting Circuitry** – Guarantees operation of up to 10 phones for suite applications, with an extra-bright message-waiting lamp
- **Redial Key** – Automatically redials the last number dialed
- **Flash Function** – Access to PBX functions
- **Hidden Programming Key** – Eliminates arbitrary reprogramming of autodial keys
- **Textured Finish** – Provides durable resistance against scratches and smudges
- **Stylish Euro Handset** – Complements room décor
- **Desk or Wall Mountable** – Provides placement flexibility

## Economical Guestroom Telephone with Data Port and Message Waiting

- **Single Line Telephones**
- **ADA Handset Volume Boost** – Compliant with HAC/VC and FCC requirements
- **Data Port** – Easy access for laptop modem or fax machine use
- **Raised Red Message Waiting Lens** – Easily seen from any area in the guestroom
- **Paper Faceplate** – Allows user-friendly customization
- **Flash Function** – Access to PBX functions
- **Textured Finish** – Provides durable resistance against scratches and smudges
- **Stylish Euro Handset** – Complements room décor
- **Desk or Wall Mountable** – Provides placement flexibility

### SPECIFICATIONS

<b>Standard Colour:</b> . . . . .	Ash and Black	<b>Signaling:</b> . . . . .	Standard 12 tone
<b>Footprint:</b> . . . . .	6.25" x 9.0"		DTMF/pulse
<b>Weight:</b> . . . . .	2.3 lbs.	<b>Flash Timing:</b> . . . . .	600 ms
<b>Packaging:</b> . . . . .	12 per carton	<b>Ringer Equivalence:</b> . . . . .	Z
<b>Faceplate Size:</b> . . . . .	8.75" x 3.13"	<b>Cabling:</b> . . . . .	2 pair minimum
<b>FCC Specifications:</b> . . . . .	Meet or exceeds	<b>Registered Connector:</b> . . . . .	USOC RJ-11
	Part 15, Subpart J,	<b>Handset:</b> . . . . .	Hearing Aid compatible
	Class A, Part 68		Standard or Euro type
<b>Safety Standard:</b> . . . . .	ETL and CE	<b>Handset Cord:</b> . . . . .	10-foot coil cord
<b>Operating Voltage:</b> . . . . .	24 to 56 VDC	<b>Line Cord:</b> . . . . .	15-foot, 1 pair
	Non-Polarity		

### SPECIFICATIONS

<b>Standard Colour:</b> . . . . .	Ash and Black	<b>Signaling:</b> . . . . .	Standard 12 tone
<b>Footprint:</b> . . . . .	4.75" x 9.0"		DTMF/pulse
<b>Weight:</b> . . . . .	2.3 lbs.	<b>Flash Timing:</b> . . . . .	600 ms
<b>Packaging:</b> . . . . .	12 per carton	<b>Ringer Equivalence:</b> . . . . .	Z
<b>Faceplate Size:</b> . . . . .	8.75" x 3.13"	<b>Cabling:</b> . . . . .	1 pair minimum
<b>FCC Specifications:</b> . . . . .	Meet or exceeds	<b>Registered Connector:</b> . . . . .	USOC RJ-11
	Part 15, Subpart J,	<b>Handset:</b> . . . . .	Hearing Aid compatible,
	Class A, Part 68		Standard Euro type
<b>Safety Standard:</b> . . . . .	ETL and CE	<b>Handset Cord:</b> . . . . .	10-foot coil cord
<b>Operating Voltage:</b> . . . . .	24 to 56 VDC	<b>Line Cord:</b> . . . . .	15-foot, 1 pair
	Non-Polarity		

### Part Numbers

NUG31739 . . . . .	Ash
NUG317391 . . . . .	Black

### Part Numbers

NUG31039 . . . . .	Ash
NUG310391 . . . . .	Black



Continuing the tradition.

To learn more, or to place an order, please visit [www.Teledex.com](http://www.Teledex.com), call +1 719 638 8821 or email [sales@teledex.com](mailto:sales@teledex.com).