



156-00635

Cable Tie and Edge Clip, 50lb, 7.9", EC4A Panel Thickness .04 -.12", PA66UV Tie, HIRHS MNT, 100/pk

Article Number: 156-00635

Part Number: 156-00635

Type: T50REC4A



Base Data

Part No. 156-00635

Type T50REC4A

Color Black (BK)

Features HellermannTyton's UV stabilized tie and edge clip assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Identification Plate Position none

Releasable Closure (Yes/No) No

Typical Application The UV stabilized tie and edge clip assemblies are ideal for use where holes are not available or where adhesives are not strong enough. Edge clips are widely used for fixing and bundling cables and wires in the automotive, harness making, panel building and renewable energy industry.

Product Dimensions

Min. Tensile Strength 50lbs / 225N

Length (L) 7.9" / 200mm

Length (L2) .55" / 14.0mm

Width (W) .18" / 4.6mm

Width (W2) .45" / 11.5mm

Height (H) .05" / 1.2mm

Height (H2) .43" / 10.8mm

Min. Ø Bundle .16" / 4.0mm

Max. Ø Bundle 1.8" / 45.0mm

Max. Panel Thickness 0.12" / 3.0mm

Min. Panel Thickness .04" / 1.0mm

Thickness 1.2mm

Material and Specifications

Material Polyamide 6.6 UV-resistant (PA66UV)

Cable Tie Polyamide 6.6 UV-stabilized (PA66UV)

Edge Clip Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

Flammability UL94 HB

Material Specification RoHS

ROHS Conformity 

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100
EAN code	4031026405049