



T50L0UVC2

Standard Cable Tie, 15.35" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number: 112-05460

Part Number: T50L0UVC2

Type: T50L



Base Data

Part No. T50L0UVC2

Type T50L

Color Black (BK)

Features

- UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures .
- Inside serrations allow for strong hold on cables and wire bundles.
- Head design provides high tensile strength with very low insertion force.
- Bent tail ensures a quick and simple installation.

Application Method Quick, simple fixing by hand or with HellermannTyton tensioning tools

Identification Plate Position none

Releasable Closure (Yes/No) No

Tie Closure plastic pawl

Typical Application Used to bundle and secure wire and cable.

Variant	Inside Serrated
----------------	-----------------

Product Dimensions

Min. Tensile Strength 50.0lbs / 225.0N

Length (L) 15.35" / 390.0mm

Width (W) 0.18" / 4.7mm

Min. Ø Bundle 0.06" / 1.5mm

Max. Ø Bundle 4.3" / 110.0mm

Thickness 1.2mm

Material and Specifications

Material Polyamide 6.6 UV-resistant (PA66UV)

US MILSPEC MS3367-2-0

Flammability UL94 V2

Material Specification HF

Operating Temperature -40 °F to +185 °F

ROHS Conformity 

Specification MIL 53421

UL Listed (US and Canada) No

UL Recognized (US and Canada) No

Logistic and Packaging

Packaging Type	pc
Pkg. Qty.	100
Carton Qty.	5000
EAN code	4031026108087
UPC	089306179733