

TFE

200° C 300/600Volts

Ratings/Approvals

300 Volts - UL Style 1180 / CSA AWM I A/B FT1

600 Volts - UL Style 1199 / CSA AWM I A/B FT1

Construction

Stranded or solid silver plated copper conductor

Extruded Polytetrafluoroethylene (PTFE)

Standard color coding available

300 Volt		
AWG (Stranding)	OD	Weight/mft
24(19)	.050"	3
22(19)	.056"	4
20(19)	.064"	6
18(19)	.070"	8
16(19)	.082"	11
14(19)	.095"	16
12(19)	.114"	25
10(37)	.146"	38

600 Volt		
AWG (Stranding)	OD	Weight/mft
24(19)	.064"	5
22(19)	.070"	6
20(19)	.078"	8
18(19)	.084"	10
16(19)	.096"	13
14(19)	.109"	19
12(19)	.128"	28
10(37)	.156"	42

Consult factory for alternate conductor and stranding options.