



Video Distribution Solutions

Miniature Coax Cable

	Description	Belden Part Number									
		Cable	Connectors 4.5 Gig BNC Compression	4.5 Gig BNC Locking	3.0 Gig BNC Compression	Compression Tool	Strip Tool	4.5 Gig BNC 3 Piece Crimp	Crimp Tool	Strip Tools	Boots
	SubMiniature, 28.5 AWG, Precision Video, Non Plenum	179DT	179DTBHD1	179DTBHDL	DB15BNCHD	CPLCRBC-BR	PS59/6/RGB	179DTBHD3	BB3PHCT	BB3PST	SLS-RGB-*
	Miniature 23 AWG Precision Video, Non Plenum and Plenum	1855A	1855ABHD1	1855ABHDL	DB15BNCHD	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
	Miniature RG59 Precision Video, Non Plenum and Plenum	1855P	1855ABHD1	1855ABHDL	DB15BNCHD	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
	Mini VideoFlex 5 Cond RG59 Snake, Non Plenum (1855A)	7789A	1855ABHD1	1855ABHDL	DB15BNCHD	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*

* indicate color when ordering, Yellow, Red, White or Black

RG-59 Coax Cable

	Description	Belden Part Number									
		Cable	Connectors 4.5 Gig BNC Compression	4.5 Gig BNC Locking	3.0 Gig BNC Compression	Compression Tool	Strip Tool	4.5 Gig BNC 3 Piece Crimp	Crimp Tool	Strip Tools	Boots
	RG59 Precision Video, Non Plenum	1505A	1505ABHD1	1505ABHDL	DB59BNCHD	CPLCRBC-BR	PS59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
	RG59 Precision Video, Plenum	1506A	1506ABHD1	1506ABHDL	—	CPLCRBC-BR	PS59/6	1506ABHD3	BB3PHCT	BB3PST	SLS-59/6
	RG59 Precision Video, Flexible	1505F	1505ABHD1	1505ABHDL	DB59BNCHD	CPLCRBC-BR	PS59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
	VideoFlex 5 Cond RG59 Snake, Non Plenum (1505A)	7796A	1505ABHD1	1505ABHDL	DB59BNCHD	CPLCRBC-BR	PS59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6

RG-6 Coax Cable

	Description	Belden Part Number									
		Cable	Connectors 4.5 Gig BNC Compression	4.5 Gig BNC Locking	3.0 Gig BNC Compression	Compression Tool	Strip Tool	4.5 Gig BNC 3 Piece Crimp	Crimp Tool	Strip Tools	Boots
	RG6 Precision Video, Non Plenum	1694A	1694ABHD1	1694ABHDL	DB6BNCHD	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
	RG6 Precision Video, Plenum	1695A	1695ABHD1	1695ABHDL	—	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
	RG6 Precision Video, Flexible	1694F	1694ABHD1	1694ABHDL	DB6BNCHD	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
	RG6 Precision Video, Dual Link	1694D	1694ABHD1	1694ABHDL	DB6BNCHD	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
	RG6 Precision Video, Indoor/Outdoor Waterblocked	1694WB	1694ABHD1	1694ABHDL	DB6BNCHD	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
	VideoFlex 5 Cond RG6 Snake, Non Plenum (1694A)	7712A	1694ABHD1	1694ABHDL	DB6BNCHD	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6

RG-7 Coax Cable

	Description	Belden Part Number			
		Cable	Connectors 4.5 Gig BNC Compression	Compression Tool	Strip Tool
	RG7 Precision Video, Non Plenum	1794A	1794ABHD1	CPLCRBC1794	PS-11

RG-11 Coax Cable

	Description	Belden Part Number					
		Cable	Connectors 3.0 Gig BNC Compression	BNC Compression Tool	Connectors 3.0 Gig F Compression	F Compression Tools	Strip Tool
	RG11 Precision Video, Non Plenum	7731A	FSNS11QHBC	SNSUNI, CPLCCT-11BNC	716SNS1P11HQ	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11
	RG11 Precision Video, Plenum	7732A	FSNSHBCPLA	SNSUNI, CPLCCT-11BNC	716SNS1P11HPLA	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11