

## Current Transformer Cabinets

### Current Transformer, Screw Cover, Type 3R



#### Industry Standards

UL 50, 50E Listed; Type 3R; File No. E27525  
cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA Type 3R  
IEC 60529, IP32

#### Application

Current Transformer Cabinets provide outdoor protection and security for instrument current transformers, which are frequently required for transformer-rated watt-hour metering. Cabinets can also be used as junction or service boxes and house meter, transformer, relay or terminal assemblies.

#### Features

- Dripshield top and seam-free sides, front and back
- Slip-on removable cover fastened with captivated plated steel screws along bottom edge
- Mounting studs on enclosure body
- Mounting holes on back of enclosure
- Door handles provided
- Provisions for padlocking
- No gasketing or knockouts
- Ground lug

#### Specifications

- 16, 14 or 12 gauge plated steel

#### Finish

ANSI 61 gray polyester powder paint finish inside and out over plated surfaces.

#### Accessories

See also *Accessories*.  
Industrial Corrosion Inhibitors  
Grounding Device  
Touch-Up Paint

Bulletin: A90CT

#### Standard Product

Catalog Number	AxBxC in./mm	D in./mm	E in./mm	F in./mm	G in./mm	H in./mm
A242411CT	24.00 x 24.00 x 11.00	12.19	9.00	8.00	8.00	—
	610 x 610 x 279	310	229	203	203	—
A303011CT	30.00 x 30.00 x 11.00	15.19	12.00	7.00	8.00	8.00
	762 x 762 x 279	386	305	178	203	203
A363011CT	36.00 x 30.00 x 11.00	18.19	15.00	7.00	8.00	8.00
	914 x 762 x 279	462	381	178	203	203
A363611CT	36.00 x 36.00 x 11.00	18.19	15.00	10.00	8.00	8.00
	914 x 914 x 279	462	381	254	203	203
A483611CT	48.00 x 36.00 x 11.00	24.19	21.00	10.00	8.00	8.00
	1219 x 914 x 279	614	533	254	203	203

