

Locking Pliers KLEIN-LOK®

- Multi-purpose tool - Pliers, pipe wrench, adjustable wrench, all-purpose clamp and wire cutter.
- Precision machined gripping jaws for greater holding power.
- Curved jaws with pincher grip hold firmly and securely.
- Variable pressure control with a quick turn of the adjustment screw.
- Curved jaw applies four points of pressure on any style of nut or bolt.
- Release lever quickly and easily unlocks the gripping jaws.
- Alloy steel is hardened for maximum strength and durability.
- Durable nickel plated finish provides corrosion resistance and long life.
- Maximum jaw capacity of 1-5/8" (41mm).
- Cuts up to 1/4" wires and bolts.



10410



10407

Cat.No.	Cutting Capacity	Handle Finish	Jaw Type	Maximum Jaw Capacity	Overall Length	Weight (lbs.)
10407	up to 1/4" wires and bolts	nickel-plated	curved	1-5/8" (41 mm)	7" (178 mm)	.75
10410	up to 1/4" wires and bolts	nickel-plated	curved	1-7/8" (44 mm)	10" (254 mm)	1.20

Slip-Joint Pliers

Slip-Joint Pliers

- Shear-type cutter for precision wire cutting.
- Two versatile jaw positions.
- Serrated jaws provide sure-gripping power.
- Nickel-chrome plated for long life.



D511-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Handle Finish	Handle Color	Weight (lbs.)
D511-6	6-9/16" (167 mm)	1-3/16" (30 mm)	1-3/16" (30 mm)	3/8" (10 mm)	plastic-dipped	blue	.39
D511-8	8-1/16" (205 mm)	1-3/8" (35 mm)	1-1/4" (32 mm)	7/16" (11 mm)	plastic-dipped	blue	.62
511-10	9-3/4" (248 mm)	1-3/4" (44 mm)	1-3/8" (35 mm)	15/32" (12 mm)	plain	n/a	.81
D511-10	9-7/8" (251 mm)	1-3/4" (44 mm)	1-3/8" (35 mm)	15/32" (12 mm)	plastic-dipped	blue	.83

Slip-Joint Pliers – Hose Clamp

- Quickly installs and removes spring-tension hose clamps.
- Grips with either end or side of jaws for work in confined areas.
- Nickel-chrome plated for long life.



D514-8

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Handle Finish	Handle Color	Weight (lbs.)
D514-8	8-1/16" (205 mm)	1-3/8" (35 mm)	1-1/4" (32 mm)	7/16" (11 mm)	plastic-dipped	blue	.61

All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

