

# Wire Strippers/Cutters

## Features:



## Wire Strippers/Cutters KLEIN-KURVE®

### Additional Features:

- Easy-to-read markings.
- Precision shear-type blades.
- Cleanly shears 6-32 and 8-32 screws.



11055

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Screw Shearing	Weight (lbs.)
11053	blue/red	7-1/8" (181 mm)	6 – 12 AWG stranded (10 mm <sup>2</sup> – 2.5 mm <sup>2</sup> )	6-32 & 8-32	.34
11055	blue/yellow	7-1/8" (181 mm)	10 – 18 AWG solid (4.0 mm <sup>2</sup> – .75 mm <sup>2</sup> ) & 12 – 20 AWG stranded (2.5 mm <sup>2</sup> – .50 mm <sup>2</sup> )	6-32 & 8-32	.34
11057	blue/red	7-1/8" (181 mm)	20 – 30 AWG solid (.50 mm <sup>2</sup> – .14 mm <sup>2</sup> ) & 22 – 32 AWG stranded (.34 mm <sup>2</sup> – .05 mm <sup>2</sup> )	6-32 & 8-32	.32

## Dual NM Cable Strippers/Cutters KLEIN-KURVE®

### Additional Features:

- 10/2, 12/2, and 14/2 stripping slots quickly remove outer jacket of Type NM-B nonmetallic-sheathed cable.
- Stripping holes easily remove insulation on 10, 12, and 14 AWG lead wire.
- Precision staggered blades for square, clean cuts on solid copper wire.
- Narrow nose fits into tight places.
- Precision shear-type blades for square, clean cuts on solid copper wire.



**SOLID**



K1412

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM-B Cable	Screw Shearing	Weight (lbs.)
K1210	yellow/orange	7-3/4" (197 mm)	10 & 12 AWG solid (4.0 mm <sup>2</sup> & 2.5 mm <sup>2</sup> )	10/2 & 12/2	6-32 & 8-32	.43
K1412	yellow/white	7-3/4" (197 mm)	12 & 14 AWG solid (2.5 mm <sup>2</sup> & 1.5 mm <sup>2</sup> )	12/2 & 14/2	6-32 & 8-32	.41

All dimensions are in inches and (millimeters).

**⚠WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**⚠WARNING:** Never use on or near live electrical circuits.

**⚠WARNING:** Always wear approved eye protection.

