


Cushion-Grip Nut Driver Sets

4-Piece Cushion-Grip Nut Driver Set

Additional Features:

- Set contains: 630-1/4, 630-5/16, 630-3/8, 630-9/16.
(See individual tool listings for more details.)

NEW!

Cat. No.	Set Contains					Weight (lbs.)
633						1.30
Cat. No.	Color Code	Hex Size Metric	Shaft Length	Overall Length		
630-1/4	red	1/4"	3" (76 mm)	6-3/4" (171 mm)		
630-5/16	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)		
630-3/8	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)		
630-9/16	orange	9/16"	4" (102 mm)	9-3/8" (238 mm)		



633

2-Piece Cushion-Grip Stubby Nut Driver Set – 1-1/2" Shafts

- Stubby nut drivers allow for work in close quarters.
- Set contains: 610-1/4, 610-5/16.
(See individual tool listings for more details.)



610

Cat. No.	Weight (lbs.)
610	.20

2-Piece Hollow-Shaft Magnetic Tip Cushion-Grip Stubby Nut Driver Set – 1-1/2" Shafts

Additional Features:

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Stubby nut drivers allow for work in close quarters.
- Set contains: 610M-1/4M, 610M-5/16M.
(See individual tool listings for more details.)



Cat. No.	Weight (lbs.)
610M	.20

2-Piece Magnetic Tip Cushion-Grip Nut Driver Sets

Additional Features:

- General-purpose selection of the most frequently used nut drivers.
(See individual tool listings for more details.)

Cat. No.	Set Contains	Weight (lbs.)
630M	630-1/4M, 630-5/16M	.40
646M	646-1/4M, 646-5/16M	.50




630M

7-Piece Metric Cushion-Grip Nut Driver Set – 3" Shafts

Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

Cat. No.	Set Contains					Weight (lbs.)
65160						1.50
Cat. No.	Color Code	Hex Size Metric	Shaft Length	Overall Length		
630-5mm	black	5 mm	3" (76 mm)	6-3/4" (171 mm)		
630-5.5mm	brown	5.5 mm	3" (76 mm)	6-3/4" (171 mm)		
630-6mm	red	6 mm	3" (76 mm)	6-3/4" (171 mm)		
630-7mm	orange	7 mm	3" (76 mm)	6-3/4" (171 mm)		
630-8mm	yellow	8 mm	3" (76 mm)	6-3/4" (171 mm)		
630-9mm	green	9 mm	3" (76 mm)	6-3/4" (171 mm)		
630-10mm	blue	10 mm	3" (76 mm)	6-3/4" (171 mm)		



65160

All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: NOT insulated. Will NOT protect against electrical shock.

