

TC2W4

Wiring Duct Cover Width 2.00" PVC, White, 120' / Pkg. Qty.

Article Number: 181-92011

Part Number: TC2W4

Type: TC2

Material: PVC



1. Base Data

Part No.	TC2W4
Type	TC2
Color	White

2. Product Dimensions

Length (L)	6 ft / 1.83 m
Width (W)	2.00 " / 50.80 mm

4. Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Certification	UL
CSA Certified	Yes
Flammability	self-extinguishing
Operating Temperature	+122 °F (+50 °C)

Logistic and Packaging

Packaging Type	carton
Pkg. Qty.	120 ft / 36.6 m
Carton Qty.	120 ft
UPC	08930609557

Miscellaneous

UL Recognized (US and Canada)	Yes
-------------------------------	-----

Covers

Covers for Pro-Duct wiring duct are sold separately. The covers are interchangeable among the 3 styles of duct (solid, slotted and high density).

For modular packaging, remove the last digit "4" from the HellermannTyton part number. e.g., TC1G = 1" wide cover/gray/modular packaging.



File # E64139 File # 49249

File # E64139 File # 49249

Product Selection					
Article No.	Part No.	Type	Width (W)	Color	Pkg. Qty.
			in. (mm)		ft. (6 ft. lengths)
.5" wide covers					
181-00443	TC.5W4	TC.5	.76" (19.30)	White	120 ft
181-00442	TC.5G4	TC.5	.76" (19.30)	Gray	120 ft
181-90050	TC.5BK4	TC.5	.76" (19.30)	Black	120 ft
.75" wide covers					
181-00447	TC.75W4	TC.75	1.01" (25.65)	White	120 ft
181-00446	TC.75G4	TC.75	1.01" (25.65)	Gray	120 ft
181-00445	TC.75BK4	TC.75	1.01" (25.65)	Black	120 ft
1" wide covers					
181-91008	TC1W4	TC1	1.00" (25.40)	White	120 ft
181-91004	TC1G4	TC1	1.00" (25.40)	Gray	120 ft
181-91000	TC1BK4	TC1	1.00" (25.40)	Black	120 ft
1.5" wide covers					
181-91510	TC1.5W4	TC1.5	1.50" (38.10)	White	120 ft
181-91507	TC1.5G4	TC1.5	1.50" (38.10)	Gray	120 ft
181-91503	TC1.5BK4	TC1.5	1.50" (38.10)	Black	120 ft
2" wide covers					
181-92011	TC2W4	TC2	2.00" (50.80)	White	120 ft
181-92005	TC2G4	TC2	2.00" (50.80)	Gray	120 ft
181-92001	TC2BK4	TC2	2.00" (50.80)	Black	120 ft
3" wide covers					
181-93011	TC3W4	TC3	3.00" (76.20)	White	120 ft
181-93008	TC3G4	TC3	3.00" (76.20)	Gray	120 ft
181-93003	TC3BK4	TC3	3.00" (76.20)	Black	120 ft
4" wide covers					
181-94014	TC4W4	TC4	4.00" (101.60)	White	120 ft
181-94009	TC4G4	TC4	4.00" (101.60)	Gray	120 ft
181-94003	TC4BK4	TC4	4.00" (101.60)	Black	120 ft
6" wide covers					
181-96002	TC6W4	TC6	6.00" (152.40)	White	60 ft
181-96000	TC6G4	TC6	6.00" (152.40)	Gray	60 ft
181-00448	TC6BK4	TC6	6.00" (152.40)	Black	60 ft
8" wide covers					
181-00451	TC8W4	TC8	8.00" (203.20)	White	60 ft
181-00450	TC8G4	TC8	8.00" (203.20)	Gray	60 ft
181-00449	TC8BK4	TC8	8.00" (203.20)	Black	60 ft

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.