

**Systimax Solutions**

760152389 | 360-iP-M-E-HD6B-2U-48

SYSTIMAX 360™ iPatch® Evolve High Density F/UTP Modular Panel, 48 port

Dimensions

Depth	38.10 mm 1.50 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	44.45 mm 1.75 in
Weight	0.73 kg 1.60 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent copper panel
Color	Cool gray
Includes	Cable management bar Forty-eight information outlets Four #12-24 dog point mounting screws Instruction sheet Panel Two #12 washers Two #12-24 screws
Intelligence Type	iPatch® enabled
Package, quantity	1
Total Ports, quantity	48

Mechanical Specifications

Panel Style	Straight
Material Type	ABS Polycarbonate
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications



760152389 | 360-iP-M-EHD6B-2U-48

RoHS 2011/65/EU
ISO 9001:2008

Compliant
Designed, manufactured and/or distributed under this quality management system

