



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PDUMV15

Single-Phase Metered PDU, 15A 120V, 0U Vertical Rackmount, 16 NEMA 5-15R outlets, NEMA 5-15P input plug



Highlights

- Metered single phase 15A 120V 0U 48in / 122cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15ft / 4.5m cord with NEMA 5-15P input plug
- 16 NEMA 5-15R outlets
- Toolless button mount and bolt-down bracket installation hardware included

Description

Tripp Lite single phase Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital display. Enables visual monitoring of PDU load levels to prevent overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Applications

- Ideal means of powering networking equipment in datacenters, computer rooms and network closets

Package Includes

- PDUMV15 Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information

Features

- 15A single phase 120V Metered Power Distribution Unit / PDU
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 120V input plug with 15ft / 4.5m line cord
- 0U 48in / 122cm vertical rackmount format installs using no rack spaces
- 16 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

OVERVIEW	
PDU Type	Metered
OUTPUT	
Frequency compatibility	50 / 60 Hz

Output VA	1800
Output nominal voltage	120V
Overload protection	15A
Outlet quantity / type	16 NEMA 5-15R
Outlet Type	NEMA 5-15R
INPUT	
Nominal Input Voltage(s) Supported	120V AC
PDU Input Voltage	100; 120; 127
Maximum Input Amps (A)	15
PDU Plug Type	NEMA 5-15P
Input cord length (ft.)	15
Input cord length (m)	4.57
Voltage compatibility (VAC)	120
Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Switches	Lighted on/off switch with integrated safety cover
Front panel LEDs	Digital LED current monitor display
PHYSICAL	
Shipping weight (lbs)	4.2
Shipping weight (kg)	1.91
Unit Dimensions (HWD/in)	3 x 48 x 1.5
Unit Dimensions (HWD/cm)	7.62 x 121.92 x 3.81
Shipping Dimensions (HWD/in)	51.5 x 3.5 x 2.5
Shipping Dimensions (HWD/cm)	130.81 x 8.89 x 6.35
Unit weight (lbs)	3.8
Unit weight (kg)	1.72
Material of construction	Aluminum
Style	Vertical Rackmount, Wallmount, Raceway, Workbench
Form factors supported	Vertical (0U) mounting in rack enclosures, horzional mount in raceways and a variety of other applications
PDU Form Factor	Vertical (0U)
SPECIAL FEATURES	
Appearance	Black housing with digital current meter display
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant

WARRANTY**Product Warranty Period
(Worldwide)**

2-year limited warranty

Related Items**Optional Products**

Related Model	Description	Qty.
P006-006-13LA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Left Angle)	1
P006-006-13RA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Right Angle)	1
P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P030-002-5	5-Pack of 2-ft. 18AWG Power Cords NEMA 5-15P to IEC-320-C13)	1
P006-003	3-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-004	4-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-004-BL	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Blue Connectors	1
P006-004-GN	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Green Connectors	1
P006-004-RD	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Red Connectors	1
P006-004-YW	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Yellow Connectors	1
P006-006	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-006-2	6-ft. AC Power Splitter Cable (NEMA 5-15P to 2 x IEC-320-C13)	1
P006-006-515MF	6 ft. Piggyback Power Cord (NEMA 5-15P/R to IEC-320-C13)	1
P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P006-010	10-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?variables.txtModelID=3458.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.