



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SR2POST25

### 25U 2-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment



#### Highlights

- 25U 2-post open frame rack
- Black aluminum with round threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

#### Description

SmartRack 2 post open frame racks are ideal for space constrained or cost conscious 19-inch rack mount applications. Multiple units can be bolted together side by side.

#### Package Includes

- SR2POST25
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual

#### Features

- Supports 800lbs of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

#### Specifications

PHYSICAL	
Installed whole system maximum rack depth (inches)	4.8
Installed whole system maximum rack depth (cm)	12.19

Installed whole system total rack space height (rack spaces)	25U
Shipping weight (lbs)	24
Shipping weight (kg)	10.89
Shipping Dimensions (HWD/in)	7 x 3 x 49
Shipping Dimensions (HWD/cm)	17.78 x 7.62 x 124.46
Unit weight (lbs)	23
Unit weight (kg)	10.43
Unit Dimensions (cm)	124.46 x 51.56 x 12.07
Unit Dimensions (in)	49 x 20.3 x 4.75 (14" total depth with support base)
Color	Black
Weight Capacity - Stationary (lbs)	800
Weight Capacity - Stationary (kg)	362.9
<b>CERTIFICATIONS</b>	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
<a href="#">B019-000</a>	KVM Switch Accessories - 2-Post Rackmount Bracket for B020,B021, B040, and B070 Consoles and KVM Consoles	1
<a href="#">B020-U08-19-IP</a>	Console KVM Switch - 8-Port NetDirector 1U Rackmount Console IP KVM Switch w/17" LCD	1
<a href="#">B021-000-17</a>	Rackmount Console - 1U Rackmount Console with 17" LCD	1
<a href="#">B021-000-19</a>	Rackmount Console - 1U Rackmount Console with 19" LCD	1
<a href="#">B021-000-19-SH</a>	Rackmount Console - 1U Short-Depth Rackmount Console with 19" LCD	1
<a href="#">B040-008-19</a>	NetController 19" VGA Console KVM Switch - 8 Port	1
<a href="#">B040-016-19</a>	NetController 19" VGA Console KVM Switch - 16 Port	1
<a href="#">N252-012</a>	12-Port Cat6 Patch Panel 568B	1
<a href="#">N252-024</a>	24-Port Cat6 Patch Panel 568B	1
<a href="#">N252-048</a>	48-Port Cat6 Patch Panel 568B	1

<a href="#">SRBOLTDOWN</a>	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	1
<a href="#">SRCABLEDUCTVRT</a>	6-ft. (1.8 m) Vertical Cable Manager (Double finger duct with cover; toolless mounting.)	1
<a href="#">SRCABLEDUCT1U</a>	1U Horizontal Cable Manager (Finger duct with cover.)	1
<a href="#">SRCABLELADDER</a>	10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder (Includes 2 sections; requires SRCABLETRAY.)	1
<a href="#">SRCABLERINGVRT</a>	6-ft. (1.8 m) Vertical Cable Manager (Flexible ring type; toolless mounting.)	1
<a href="#">SRCABLERING1U</a>	1U Horizontal Cable Manager (Flexible ring type.)	1
<a href="#">SRCABLERING2U</a>	2U Horizontal Cable Manager (Flexible ring type.)	1
<a href="#">SRFAN3U</a>	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	1
<a href="#">SRSCREWS</a>	Threaded hole hardware kit - 50 each #12-24 screws	1
<a href="#">SRSHELF2P</a>	2U Cantilever Fixed Shelf (60 lb / 27 kg capacity; 18-in. / 457 mm depth.)	1
<a href="#">SRXFAN3U</a>	3U Fan Panel, 230V (3 high-performance fans; 210 CFM; C14 inlet.)	1
<a href="#">UPSHDEARKIT</a>	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb / 29 kg from front vertical rails in 4-post or 2-post racks and enclosures. )	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?variables.txtModelID=4021](http://www.tripplite.com/en/products/model.cfm?variables.txtModelID=4021).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.