

Fiber Optic Jumper, 1 F, Pigtail to SC, Tight-Buffered Cable, Riser, 900 µm

Single-mode (OS2), 2 m

CORNING

Simplex cable assemblies are offered with a variety of connector combinations. Connector options include LC, SC, FC and ST® Compatible. RoHS compliant cables with riser-rated jackets are available in 3.0 mm, 2.0 mm, 1.6 mm and 900 µm.

Additional detailed furcation images are available in the Cable Assembly Family Specification Sheet.

Many of our fiber optic cable assemblies are highly configurable. If you don't see what you are looking for here, please review the ordering matrix contained in the family spec sheet, or contact Customer Care at 1-800-743-2671.

Features and Benefits

Flame-retardant jacket

Rugged and durable

Geometry is verified

Product performance over temperature variations is guaranteed

100% visual inspection per IEC 61300-3-35

Product performance consistency is guaranteed

Corning advantage

Integrated developer and manufacturer of cable, connectors and fiber to ensure overall cable assembly performance

Specifications

General Specifications

Application	Vertical Riser, General Building Applications
Cable Type	Tight-Buffered
Flame Rating	Riser (OFNR)
Cable Assembly Type	Single Fiber
Fiber Category	Single-mode (OS2)

Design - Connector A

Connector Type	No connector
----------------	--------------

Fiber Optic Jumper, 1 F, Pigtail to SC, Tight-Buffered Cable, Riser, 900 µm

Single-mode (OS2), 2 m

CORNING

Design - Connector B

Connector Type	SC
Ferrule	Ceramic
Housing Material	Composite
Housing Color	Blue
Boot Color	Blue

Optical Specifications - Connector B

Polish	UPC
Reflectance, Typical	≤ -58 dB
Insertion Loss, Typical	0.15 dB

Cable Design

Fiber Count	1
Outer Jacket Color	Yellow

Mechanical Characteristics Cable

Nominal Outer Diameter	900 µm (0.4 in)
------------------------	-----------------

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	005801R4131002M
Product Description	Fiber Optic Jumper, 1 F, Pigtail to SC, Tight-Buffered Cable, Riser, 900 µm, Single-mode (OS2), 2 m
Length	2 m (6.6 ft)

CORNING

Fiber Optic Jumper, 1 F, Pigtail to SC, Tight-Buffered Cable, Riser, 900 μ m

Single-mode (OS2), 2 m

CORNING

Shipping Information

Units per Delivery	1/1
--------------------	-----



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.