

# UniCam® Connector, ST® Compatible, Organizer Pack

Organizer pack, 50 µm multimode (OM2)

CORNING

Corning Cable Systems UniCam® Multimode Standard-Performance Connectors offer optical performance in a fast, easy field-termination solution ideal for fiber-to-the-workstation applications where setup and teardown time is critical. The high-precision mechanical splice technology enables fiber optic networks to be installed quickly and cost effectively. The lightweight, handheld installation tool and the high-performance cleaver virtually eliminate human variability from installation, ensuring terminations are right the first time, every time. This kit was designed with consideration for network installers, from the cleaver, with its integrated fiber scrap bin and dual-clamp precision hold, to the installation tool, with its immediate go/no-go feedback signal. Installation is as easy as strip, clean, cleave, cam and crimp, with exceptional optical performance guaranteed. Every UniCam Connector is guaranteed to meet the published specification at the time of installation or Corning Cable Systems will replace it.



Part Number: 95-050-50-Z

## Features and Benefits

### Factory-polished end face

Consistent optical performance

### Fast termination and no consumables

Low installation cost

### Minimum insertion loss

Optimum optical performance

## Standards

### Approval and Listings

Compliant with EIA/TIA 568-B.3

### Intermateability

Connectors are FOCIS compliant with TIA/EIA 604-3 and IEC61754-4

CORNING

# UniCam® Connector, ST® Compatible, Organizer Pack

Organizer pack, 50 µm multimode (OM2)



## Specifications

General Specifications	
Technology	No-Epoxy/No-Polish
Keyed	No
Product Type	Field-Installable Connectors
Corning Logo	Yes
Packaging	Organizer Pack
Fiber Category	50 µm MM (OM2)

Temperature Range	
Operation	0 °C to 60 °C, meets TIA/EIA 568-B.3 (32 °F to 140 °F, meets TIA/EIA 568-B.3)

Chemical Characteristics	
RoHS	Free of hazardous substances according to RoHS 2002/95/EG

## Ordering Information

Part Number	95-050-50-Z
Product Description	UniCam® Standard-Performance Connector, ST® Compatible, 50 µm multimode (OM2), ceramic ferrule, logo, organizer pack, amber housing, black boot

## Shipping Information

Units per Delivery	25/1
Package Contents	25 connectors, 25 boots (900 µm)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.