UniCam® Connector, LC, Organizer Pack

Organizer Pack, 50 µm multimode (OM3/OM4 compatible)



Corning Cable Systems UniCam® High-Performance Connectors offer best-in-class optical performance in a fast, easy field-termination solution. These high-precision connectors guarantee exceptional insert loss - 0.1 dB typical/0.5 dB maximum per connector pair for multimode, 0.2 dB typical/0.5 dB maximum per connector pair for single-mode. Installation of an LC, SC, or ST® Compatible Connector can be accomplished in about 45 seconds with the UniCam High-Performance Tool Kit. The lightweight, handheld installation tool and the highperformance cleaver virtually eliminate human variability from installation, ensuring terminations are right, the first time, every time. This kit was designed with consideration for the network installers, from the cleaver, with its integrated fiber scrap bin and dual-clamp precision hold, to the installation tool, with its immediate go/no-go feedback signal. Installation is as easy as strip, clean, cleave, cam and crimp, with exceptional optical performance guaranteed. Every UniCam Connector is guaranteed to meet the published specification at the time of installation or Corning Cable Systems will replace it.



Part Number: 95-050-99-X-Z

Features and Benefits

Broad operating temperature (-40° to +75°C) Utility and flexibility

Factory-polished end face Consistent optical performance

Fast termination and no consumables Low installation cost

Minimum insertion loss
Optimum optical performance

Standards

Approval and Listings Passed EIA/TIA 568-B.3

Intermateability Connectors are FOCIS compliant with TIA/EIA 604-10A and IEC61754-20

UniCam® Connector, LC, Organizer Pack

Organizer Pack, 50 µm multimode (OM3/OM4 compatible)



Specifications

General Specifications	
Technology	No-Epoxy/No-Polish
Keyed	No
Product Type	Field-Installable Connectors
Corning Logo	Yes
Packaging	Organizer Pack
Fiber Category	50 μm MM (OM3/OM4 compatible)

Temperature Range	
Operation	-40 °C to 75 °C exceeding EIA/TIA 568-B.3 (-40 °F to 167 °F exceeding EIA/TIA 568-B.3)

Chemical Characteristics	
RoHS	Free of hazardous substances according to RoHS 2002/95/ EG

Ordering Information

Part Number	95-050-99-X-Z
Product Description	UniCam® High-Performance Connector, LC, 50 µm multimode (OM3/OM4 compatible), ceramic ferrule, logo, organizer pack, black housing, aqua boot

Shipping Information

Units per Delivery	25/1
Package Contents	25 connectors, 25 triggers, 25 boots (900 μm)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

