

# Closet Splice Housing (CSH)

3 rack units, holds (12) 0.2-in splice trays

CORNING

Corning Cable Systems Closet Splice Housing (CSH) provides storage and protection of fiber splices in individually accessible trays. The housings are used in equipment racks or equipment cabinets, 19-in (48 cm) or 23-in (58 cm), and in the transition splice between outdoor-rated and riser/plenum-rated cable at a building entrance. Pigtail splicing is accomplished when the CSH is used in conjunction with a rackmount housing. The CSH is available in 3-rack-space tall and 5-rack-space models. A sliding shelf provides access to splice trays and routing guides. The housing has top and bottom rear removable access panels for vertical pigtail entry from the CLSSC-03U or CLSSC-04U housings and lockable front and rear doors (with the optional lock kits).

## Features and Benefits

### Universal cable clamp

Cable strain-relief

### Open-side design

Easy fiber egress

### Projection- or flush- mountable

Various installation options

### Multiple grommeted cable entry ports

Installation options and protection

## Specifications

General Specifications	
Application	Enterprise Networks
Mounting Type	Rack 19-in, Rack 23-in
Product Type	Rack-Mountable Hardware

# Closet Splice Housing (CSH)

3 rack units, holds (12) 0.2-in splice trays

CORNING

## Design - Hardware

Housing Color	Black
Housing Type	CSH
Height Unit	3U
Locking Availability	Front or rear
Splice Tray Options	Up to (12) category 2R, 2S, or 2M

## Mechanical Characteristics

Dimensions (HxWxD)	13.3 cm x 43.2 cm x 30.5 cm (5.25 in x 17 in x 12 in)
--------------------	---

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

## Ordering Information

Part Number	CSH-03U
Product Description	Closet Splice Housing (CSH), 3 rack units, holds (12) 0.2-in splice trays

## Shipping Information

Units per Delivery	1/1
Package Contents	Housing with 19-in mounting ears; splice tray stacker with 24-in Velcro strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, #12-24; 4 mounting screws, M6; 4 cage nuts, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpaper, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32
Shipping Weight	2.7 kg (6 lb)

CORNING

# Closet Splice Housing (CSH)

3 rack units, holds (12) 0.2-in splice trays



CORNING

## Notes



**Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA**

**800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)**

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING